


Ovaj prijevod sastoji se od Stranica 1 / Listova 4
Broj-OV: 0080/2016
Datum: 10.02.2016.
Naziv dokumenta: Uni-Jet 75
Ime: VIK-DENTAL D.O.O.

Ovjereni prijevod s engleskog jezika



Model	Uni-Jet 75 s kutijom i upravljačkom pločom	13.1
Nazivni napon	230 V $\pm$ 5%	
Nazivna frekvencija	50 Hz	
Nazivna struja	3,1 A	
Razred izolacije	Razred I	
Vrsta uređaja	B	
Operativni uvjeti	Kontinuirani rad	
Zaštita od prodora tekućina	obična	
Stupanj zaštite od električnog udara	tip B 1:	
Motor je zaštićen toplinskim prekidačem		
Izlazna snaga	0,4 kW	
Maksimalni protok	12501 / min	13.3
Maksimalna glava za kontinuirani rad	1300 mm H ₂ O	
Razina zvučnog tlaka	58 dB(A)*	13.2
Ostali naponi dostupni na zahtjev: 240 V $\sim$ 50 Hz 2,95 A - 220 V $\sim$ 60 Hz 3,5 A - 120 V $\sim$ 60 Hz 6,0 A - 110 V $\sim$ 60 Hz 7,0 A - 100V 60 Hz $\sim$ 7,0 A		
Ovaj uređaj ne može raditi u prisustvu anestetičke smjese zapaljive sa zrakom, kisikom ili dušikovim oksidom		
Bakteriološki filter je također dostupan za filtriranje ispuštenog zraka		

	Izmjenična struja	IEC 417-5032
	Uzemljenje	IEC 417-5019
	Aparat tipa B	IEC 878-02-02
	OTVOREN (isključen iz glavnog električnog napajanja)	IEC 417-5008
	ZATOOREN (spojen na glavno električno napajanje)	IEC 417-5007
	Opasni napon	IEC 878-03-01

*Razina zvučnog tlaka s kanaliziranim zrakom testirana prema normi ISO 3746-1979(E).

Parametri: r=1 – Pozadinski zvuk $\leq$ 51 dB (A) - Instrument: Bruel & Kjeer tip 2232.
Proizveo CATTANI S.P.A. - PARMA - ITALIJA

Ja, Michael Mile Nekich, stalni sudski tumač za engleski jezik, imenovan rješenjem predsjednika Županijskog - Trgovačkog suda u Zagrebu broj 4 Su-1000/13 od 28. lipnja 2013. potvrđujem da gornji prijevod potpuno odgovara izvorniku sastavljenom na engleskom jeziku.

Broj-OV: 0080/2016
U Zagrebu, 10.02.2016.

M. Nekich



General running data Dental Aspirator

Model	Uni-Jet 75 with box and control panel
Rated voltage	230 V $\sim$ $\pm$ 5%
Rated frequency	50 Hz
Rated current	3,1 A
Insulation class	Class I
Type of appliance	B
Operating conditions	continuous operation
Protection against ingress of liquids	ordinary
Degree of protection against electric shock	type B 
The motor is protected by a thermal switch	
Output power	0,4 kW
Maximum flow	1250 l/min
Maximum head for continuous operation	1300 mm H ₂ O
Sound pressure level	58 dB(A)*
Other voltages available on request: 240 V $\sim$ 50 Hz 2,95 A - 220 V $\sim$ 60 Hz 3,5 A - 120 V $\sim$ 60 Hz 6,0 A - 110 V $\sim$ 60 Hz 7,0 A - 100 V $\sim$ 60 Hz 7,0 A	
This appliance cannot work in the presence of an anaesthetic mixture flammable with air, oxygen or nitrous oxide	
A bacteriological filter is also available to filtrate the exhausted air	

	Alternating current	IEC 417-5032
	Earthing	IEC 417-5019
	Appliance Type B	IEC 878-02-02
	OPEN (disconnected from the main electrical supply)	IEC 417-5008
	CLOSED (connected to the main electrical supply)	IEC 417-5007
	Dangerous voltage	IEC 878-03-01

*Sound pressure level with canalized air tested according to the standard ISO 3746-1979 (E).
Parameters: r=1 - Background noise $\leq$ 51 dB (A) - Instrument: Brüel & Kjær Type 2232.

Manufactured by CATTANI S.P.A. - PARMA - ITALY

